PicoBlade Standard Cable Assemblies

molex

Off-the-shelf PicoBlade Cable Assemblies come in a variety of cable lengths in a compact connector to support both prototyping and global production

Features and Benefits

Point-to-point single-row configurations for PicoBlade designs immediately available Support both development and production programs



PicoBlade Standard Cable Assemblies

Pin-to-pin map configurationsReduces the need to design the cable layout. Requires engineers to simply assign each signal to a pin

PicoBlade Receptacles small pitch and friction lock

Takes up less PCB real estate. Minimizes chance of accidental unmating due to vibration or mishandling

Meets 2011/65/ EU RoHS compliance Less engineering time and resources required to use

Built in ISO- and TS-16949-certified facilities Meets current market standards for using Molex connector systems

Built using UL1061 discrete wires

Applications

Consumer

Home entertainment

Home appliances

Gaming consoles

Mobile devices


Commercial Vehicle

Industrial

Process controls

Medical

Patient monitors



Mobile Devices



Home Appliances

PicoBlade Standard Cable Assemblies



Specifications

REFERENCE INFORMATION

Packaging: 50 or 100 SPQ Cable UL File No.: UL1061

Mates With: Series 53261, 53047, 53398, 53048

Designed In: Millimeters

RoHS: Yes Halogen Free: No Glow Wire Compliant: No

ELECTRICAL

Voltage (max.): 50V Current (max.): 1.0A

Contact Resistance: 20 milliohms Dielectric Withstanding Voltage: 250V AC Insulation Resistance: 100 Megohms

MECHANICAL

Contact Insertion Force (max.): 4.9N Contact Retention to Housing (min.): 4.9N Mating Force: Please see product spec Unmating Force: Please see product spec

PHYSICAL

Housing: Please see product spec Contact: Please see product spec

Plating:

Contact Area — Tin Solder Tail Area — Tin Underplating — Tin

Operating Temperature: -40 to +85°C

Ordering Information

Series No.	Component	Number of Rows	Circuits	Length (m)
<u>15134-02**</u>	PicoBlade Cable Assembly	Single	2	- 0.05, 0.10, 0.15, 0.30, 0.45, 0.60
<u>15134-03**</u>			3	
<u>15134-04**</u>			4	
<u>15134-05**</u>			5	
<u>15134-06**</u>			6	
<u>15134-07**</u>			7	
<u>15134-08**</u>			8	
<u>15134-10**</u>			10	
<u>15134-12**</u>			12	
<u>15134-14**</u>			14	

Custom Product	Description	
<u>Contact Molex</u>	Custom lengths and other options	

www.molex.com/product/picoblade.html www.molex.com/link/otscableassemblies.html