

# MINI-FIT PRODUCTS

## COMPARISON CHART

		PITCH (MM)	CURRENT	WIRE (AWG)	CONFIGURATION	FEATURES
MINI-FIT		4.20	UP TO 13.0A	16-28	Board-to-Board Wire-to-Board Wire-to-Wire	High current options, BMI options, Backshells, Cable assemblies, Pre-crimped leads, TPA capable
MINI-FIT SIGMA		4.20	UP TO 13.5A	16-24	Wire-to-Board Wire-to-Wire	Receptacles have V0 combo resin, Sealed option, multiple points of contact, slim profile design, TPA capable, Sigma receptacles mate with standard Mini-Fit headers
MINI-FIT TPA2		4.20	UP TO 13.5A	16-24	Wire-to-Board Wire-to-Wire	TPA capable, V0, V2, V2/Glow wire resin, mates with standard Mini-Fit headers and plugs *With TPA added, the connector space increases
MINI-FIT VERSA		4.20	UP TO 11.5A	16-28	Wire-to-Board Wire-to-Wire	Color options, V0 Glow wire resin combo
MINI-FIT MAX		4.20	UP TO 20.5A	14-16	Wire-to-Board	V0 Glow Wire resin combo, tangless terminals, higher current, slim profile design, has different keying and polarization from standard Mini-Fit therefore does not mate to standard Mini-Fit

