

# Mini-Lock Wire-to-Board Connector System >

The 2.50mm-pitch Mini-Lock Wire-to-Board/Wire-to-Wire Connector System offers design versatility with vertical and right-angle SMT headers, and terminal position assurance (TPA) while also providing Glow Wire options for safety and protection in the home appliance market.



### **FEATURES AND ADVANTAGES**

**Ensures that wires are fully inserted** Terminal position assurance (TPA)

Can be supplied to global home appliance makers who require glow wire material

Glow Wire capable

Seats the crimp terminal fully in the receptacle housing to reduce terminal backout

TPA feature

Meets global safety and environmental requirements

Glow Wire capable

Allows quick, automated mounting assembly on the PCB when used as a vertical header

SMT Header Terminal

Mitigates the misalignment by assisting in right mount orientation

Locating Peg (Boss)

Provides secure header retention on the PCB before soldering

Kinked pin

Protects the components on PCB from dust and water


Potting treatment (Height 2.00 to 6.00mm)

Voltage	250V	
Pitch	Pitch 2.50mm	
Glow Wire Capable	Yes	
Operating Temperature	-40 to +105°C	

Enables robust retention on the PCB when mounted as a right-angle header (in which case a different series number, 215932 is assigned)
SMT solder tab



Receptacle Housing: 51163 TPA: 51164



Header for Potting: 53517xx30



# Enables easy access to crimp applicators that are readily available in the market

Use of popular crimp terminals











# Mini-Lock Wire-to-Board Connector System >

### **APPLICATIONS**

# **Home Appliance**

Refrigerators Washers and dryers Air conditioners

#### **Industrial**

Automation equipment Vending machines

# Consumer

Fitness equipment Gaming machines Security systems

### **Automotive**

Interior/exterior lightings Audio equipment Navigation systems







Refrigerators



Vending Machines

# **SPECIFICATIONS**

### **Reference Information**

Packaging: Refer to Packaging Specifications

UL File No.: E29179 CSA File No.: LR19980 Designed In: Millimeters

RoHS: Yes Halogen Free: No Glow Wire Capable: Yes

### **Electrical**

Voltage (max.): 250V Current (max.): Refer to Current Derating Reference Information Contact Resistance (max.): 20 milliohms Dielectric Withstanding Voltage: 1000V AC/min

Insulation Resistance (min.): 1000 Megohms

#### Mechanical

Contact Insertion Force (max.): 9.8N

Contact Retention to Housing (min.): 14.7N

Mating Force (max.): 58.8N (8 circuit)

Unmating Force (min.): 7.9N (8 circuit)

Durability (max.): 30 cycles

### **Physical**

Housing:

PBTP UL94V-0 (51163, 51164, 53375, 53426) PA66 UL94V-0 (53517, 53426 GW, 51163 GW) PA9T UL94V-0 (215931, 215932) Contact: Phosphor Bronze

Plating: Pre-Tin

Contact Area (min.)- 0.9 micrometer Header Pin: Phosphor Bronze

Plating: Pre-Tin

Contact Area (min.) - 1.0 micrometer Operating Temperature: -40 to+ 105°C



# Mini-Lock Wire-to-Board Connector System >

# **CURRENT DERATING REFERENCE INFORMATION**

AWG	2-circuits	7-circuits	15-circuits
	Amps (A)	Amps (A)	Amps (A)
20	5.0	3.5	3.5
22	4.5	3.0	3.0
24	4.0	2.5	2.5
26	3.5	2.5	2.0

- (1) Values are for REFERENCE ONLY.
- (2) Current derating values are based on temperatures not exceeding 30°C.
- (3) PCB trace design can greatly affect temperature rise results in wire-to-board applications.
- (4) Data is for all powered circuits.
- (5) All data are interpolated information.

# **ORDERING INFORMATION**

Series No.	Components	AWG or Circuits	Glow Wire Capable
<u>50752</u>	Crimp Terminal	20 to 26 AWG	-
<u>51163</u>	Receptacle Housing	2 to 15	Yes
<u>51164</u>	TPA Retainer		Yes
<u>53517</u>	Vertical Header for Potting, H=17.5mm,Through Hole		Yes
<u>53375</u>	Vertical Header, H=11.5mm, Through Hole		No
<u>53476</u>	Vertical Header, H=11.5mm, Through Hole		Yes
<u>53426xx10</u>	Right-Angle Header, Through Hole		No
<u>534269xx0</u>	Right-Angle Header, Through Hole		Yes
<u>534269xx1</u>	Right-Angle Header, Through Hole		Yes
<u>215931</u>	Vertical Header, SMT		Yes
215932	Right-Angle Header, SMT		Yes

# www.molex.com/link/minilock.html